

Cadweld Multi Multiple Connection Type Mold Kit

Data Solutions

KATALOGOVÉ ČÍSLO

KITCDMV01



VLASTNOSTI

Versatile mold produces a variety of connections

Patented, self-sealing system prevents weld metal leakage

Compact compression structure enables easy alignment of conductors

Language-free instruction guide

Easy-to-use system completes welds in seconds

VLASTNOSTI PRODUKTU

Article Number: 167782

Complies With: EN IEC® 62561-1 permanent connection

Types of ERICO CADWELD MULTI Multiple Connectors							
Mold Style	Number of Battings Required	Maximum Conductor Size	Maximum Bus/Lug Size	Maximum Rebar Size, Metric	Maximum Rebar Size, US	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual
Solid or Stranded Copper Cable to Solid or Stranded Copper Cable							
SS	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
SC	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
XA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GG	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GJ	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GF	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GW	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
XB	3	50 mm ² Str; 1/0 Str	-	-	-	-	-
PP	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PK	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GE	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PG	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
TD	2	25 mm ² Str; #4 Str	-	-	-	-	-
TE	2	25 mm ² Str; #4 Str	-	-	-	-	-
TF	2	25 mm ² Str; #4 Str	-	-	-	-	-
Solid or Stranded Copper Cable to Rebar							
RG	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RH	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RK	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RD	3	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
Copper or Steel Tape to Rebar							

RF	2	-	30 x 3.5 mm	10 mm	#3	-	-
Copper Tape to Copper Tape							
BB	2	-	30 x 3.5 mm	-	-	-	-
CG	3	-	30 x 3.5 mm	-	-	-	-
BG	3	-	30 x 3 mm	-	-	-	-
EB	3	-	30 x 3 mm	-	-	-	-
Solid or Stranded Copper Cable to Copper or Steel Bus/Lug							
HA	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HC	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HS	3	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HT	3	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
GL	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LA	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LJ	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LE	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
Galvanized Steel Tape to Galvanized Steel Tape							
BB	2	-	30 x 3 mm	-	-	-	-
CG	3	-	30 x 3 mm	-	-	-	-
Solid or Stranded Copper Cable to Ground Rods							
TG	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GT	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GR	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GT	3	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GR	3	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
Copper Tape to Ground Rod							
CN	2	-	30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	2	-	30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CN	3	-	30 x 2.5 mm - 30 x 3 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	3	-	30 x 2.5 mm - 30 x 3 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
Galvanized Steel Tape to Ground Rod							

CN	3	-	30 x 0.5 mm - 30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	3	-	30 x 0.5 mm - 30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte