

3x Temperature and 1x Humidity Sensor

Data Solutions

KATALOGNUMMER

EA9105



3x Temperature and 1x Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

FUNKTIONER

3x Temperature and 1x Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +- 5 %

Second and Third Temperature Sensor with 950 mm cable

PRODUKTEGENSKABER

Product Type: Sensor

Works With: RackPower

Højde: 270mm

Pakke mængde: 1

Plug Type: RJ45

Produktfamilie: Enlogic

Removable Input Cable: No

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE