

# Enlogic Basic PDU

## Data Solutions



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

### FUNKTIONER

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

### SPECIFIKATIONER

Table 1/6

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	Socket Quantity	Farve
EB0860	Enlogic	Basic PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black
EB09JA	Enlogic	Basic PDU	Socket Strip	(18) C13/C15, (18) C13/C15/C19/C21	36	Black
EB0360	Enlogic	Basic PDU	Socket Strip	(16) C13/C15	20	Black

Table 2/6

Katalognummer	Switched Outlets	Cable Length	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Interrupt Rating
EB0860	No	3000mm	20 A, 1-pole, Hy-MagA	17.3 kVA North America, 22.1 kVA International	6	

Katalognummer	Switched Outlets	Cable Length	Circuit Breaker	Power Rating	Circuit Breaker Quantity	InterruptRating
EB09JA	No	1800mm	20 A, 1-pole, Hy-MagA	34.6 kVA North America, 43.5 kVA International	12	
EB0360	No	3000mm	16 A, 1-pole, Hy-Mag	7.4 kVA	2	5kAIC

Table 3/6

Katalognummer	Nominal Power Output	Nominal spænding	Number of Output Voltages	Antal faser	On/Off Switch Included	Amperage (Derated Amperage)
EB0860	230VAC	415V			No	30 A (24 A) North America, 32 A International
EB09JA	230VAC	415V	36		No	60 A (48 A) North America, 63 A International
EB0360	230VAC	230V	20	1	No	32 A

Table 4/6

Katalognummer	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Materiale
EB0860	208 – 230VAC	0U	IEC 60309 530P6/532P6	None	No	Stål
EB09JA	208 – 230VAC	0U	IEC 60309 560P6/563P6	None	No	Stål
EB0360	230VAC	0U	IEC 60309 332P6 (IP44)	None	No	Stål

Table 5/6

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EB0860	Struktur Pulvermaling	1490mm	56mm	55mm		1
EB09JA	Struktur Pulvermaling	965mm	114mm	75mm		1
EB0360	Struktur Pulvermaling	817mm	52mm	53mm	3.6kg	1

Table 6/6

Katalognummer	Input Cable Length
---------------	--------------------

EB0860	3m
EB09JA	1.8m
EB0360	3m

## YDERLIGERE PRODUKTOPLYSNINGER

---

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**