

# Socket Strip, SCHUKO

Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.



## CERTIFICERINGER



## FUNKTIONER

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

## SPECIFIKATIONER

**Materiale:** Aluminium; Polyamide

**Farve:** Grey

**Product Type:** Socket Strip

Table 1/2

Katalognummer	Stiktype	Socket Quantity	Switched Outlets	Spænding AC	Function	Pakke mængde
60110-207	SCHUKO	12	Yes	230V		1

Katalognummer	Stiktype	SocketQuantity	Switched Outlets	Spænding AC	Function	Pakke mængde
60110-202	SCHUKO	9	No	230V		1
60110-266	SCHUKO	6	No	230V	Transient Protection, Mains Suppression Filter	1
60110-203	SCHUKO	12	No	230V		1
60110-204	SCHUKO	15	No	230V		1
60110-205	SCHUKO	19	No	230V		1
60110-217	SCHUKO	6	No	230V	Fault Current Protection, Overcurrent Protection	1
60110-201	SCHUKO	4	No	230V		1
60110-206	SCHUKO	8	Yes	230V		1
60110-208	SCHUKO	15	Yes	230V		1
60110-216	SCHUKO	6	No	230V	Fault Current Protection	1
60110-209	SCHUKO	19	Yes	230V		1
60110-210	SCHUKO	8	No	230V	Transient Protection	1
60110-211	SCHUKO	9	No	230V	Transient Protection	1
60110-214	SCHUKO	7	No	230V	Mains Suppression Filter	1
60110-200	SCHUKO	3	No	230V		1
60110-212	SCHUKO	6	No	230V	Overcurrent Protection	1

Table 2/2

Katalognummer	Dybde	Finish	Length
60110-207	44mm	Anodized	947.5mm
60110-202	44mm	Anodized	438.5mm
60110-266	44mm	Anodized	438.5mm
60110-203	44mm	Anodized	947.5mm
60110-204	44mm	Anodized	1202mm
60110-205	44mm	Anodized	1753mm
60110-217	88mm	Anodized	438.5mm

Katalognummer	Dybde	Finish	Length
60110-201	44mm	Anodized	210mm
60110-206	44mm	Anodized	438.5mm
60110-208	44mm	Anodized	1202mm
60110-216	88mm	Anodized	438.5mm
60110-209	44mm	Anodized	1753mm
60110-210	44mm	Anodized	438.5mm
60110-211	44mm	Anodized	947.5mm
60110-214	44mm	Anodized	438.5mm
60110-200	44mm	Anodized	184mm
60110-212	75mm	Anodized	438.5mm

## YDERLIGERE PRODUKTOPLYSNINGER

Please order mounting bracket for vertical mounting separately.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelser af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**