

Angle Bracket



FEATURES

Provides an attachment for nVent CADDY Speed Link assemblies, wire, threaded rod, S-hooks, or chain from concrete or wood

SPECIFICATIONS

Finish: Hot-Dip Galvanized


Table 1/2

Catalog Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Height (H)	Length (L)	Width (W)	Thickness (T)
AB77	7 mm	7 mm	37 mm	37mm	25 mm	3 mm
AB97	9 mm	7 mm	37 mm	37mm	25 mm	3 mm
AB711	11 mm	7 mm	37 mm	37mm	25 mm	3 mm
AB1111	11 mm	11 mm	37 mm	37mm	25 mm	3 mm

Table 2/2

Catalog Number	Static Load
AB77	700N
AB97	700N
AB711	700N
AB1111	700N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

