

XL-TRACE PRE-TERMINATED, LOW SMOKE ZERO HALOGEN SELF-REGULATING CABLE KIT



nVent RAYCHEM kits comprise a 10XL2-ZH self-regulating heating cable with a pre-installed low smoke zero halogen cold lead cable of 4 m, cold lead to heater cable splice and end seal. The kits are available in fixed lengths between 3-30 m. Factory terminated and electrically tested.

FEATURES & BENEFITS

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Energy efficient: self-regulating cable, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible

Easy to install, pre-terminated kits

Zero halogen: IEC60754-1 tested and compliant

Improved self-extinguishing properties under the IEC62395 flammability test

SPECIFICATIONS

Heating Cable Technology Self-Regulating

Supply Voltage 220 – 240 V

Nominal Power Output @ 5°C, 230V 10 W/m

Max Continuous Exposure Temperature, Power On 65 °C

Outer Jacket Material Low Smoke Zero Halogen

Color Plum

Ground Path Type Braid

Min Installation Temperature -40 °C

Nominal Height 6.8 mm

Nominal Width 13.8 mm

Cold Lead Length 4 m

Table 1/1

Catalog Number	Item Name	Length
1244-021274	10XL2-ZH-KIT-12m	12 m
1244-021271	10XL2-ZH-KIT-3m	3 m
1244-021272	10XL2-ZH-KIT-5m	5 m
1244-021275	10XL2-ZH-KIT-16m	16 m
1244-021273	10XL2-ZH-KIT-8m	8 m
1244-021276	10XL2-ZH-KIT-20m	20 m
1244-021277	10XL2-ZH-KIT-25m	25 m
1244-021278	10XL2-ZH-KIT-30m	30 m

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.