

# Crimping Compression Tool Die, Type M2, Heavy-Duty DIN46235, #2 Stranded, 35 mm<sup>2</sup> Stranded

## Data Solutions

### CATALOG NUMBER

---

**PKM235**



### FEATURES

---

Suitable for cable lugs and connectors

### PRODUCT ATTRIBUTES

---

Article Number: 716945

Lug/Connector Type: Heavy-Duty DIN46235

Conductor Size: #2 Stranded; 35 mm<sup>2</sup> Stranded

Crimping Width: 5mm

Tool: M2H; M2M

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**