

NRG-DM DIGITAL TIMER THERMOSTAT

nVent RAYCHEM NRG-DM is a digital timer thermostat for electrical floor heating equipped with a large display and intuitive software.



FEATURES & BENEFITS

Easy to use, intuitive navigation: large LCD display with blue back light

3 operating modes: event mode or weekly schedule to reduce energy; boost mode or temporary override; constant mode

Energy efficient adaptive function

Optimum heat management, with 4 sensor modes

Reliable during long life: 12 year total care warranty available, maintenance free

SPECIFICATIONS

Adjustable Differential No

Regulation Type On/Off

Max Contact Voltage 230 V

Max Contact Load 13 A

Sensor/Feeler Type Resistance Sensor

Temperature Control Class IV

Control Characteristic PID

Remote Operation No

Switching Program Quantity 7

Power Consumption, Standby 0.4 W

IP Rating IP21

RAL Number 9010

Color Clear White

IFTTT Support Available No

Clock Type Day Clock

Clock Model Digital

Self Learning Yes

Depth 40 mm

Table 1/1

Catalog Number	Item Name	Power Supply	Measuring Range	Height	Width
1244-015152	R-NRG-DM	230 V	5 – 40 °C	82 mm	82 mm

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.