

ICESTOP SELF-REGULATING CABLE KIT



nVent RAYCHEM IceStop self-regulating trace heating cable kits provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

FEATURES & BENEFITS

Simple to design

Easy to install, pre-terminated kits: 5 - 30 m, each with 8 m power cable, GM-RAKE fixing bracket and RayClic end seal

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Heating Cable Technology Self-Regulating

Supply Voltage 220 – 240 V

Nominal Power Output, In Air @ 0°C, 230V 18 W/m

Nominal Power Output, In Ice Water @ 0°C, 230V 36 W/m

Outer Jacket Material Modified Polyolefin

Color Black

Ground Path Type Braid

Min Installation Temperature -18 °C

Nominal Cable Weight 120 g/m

Nominal Width 14 mm

Nominal Height 6 mm

Max Continuous Exposure Temperature, Power On 65 °C

Max Intermittent Exposure Temperature, Power On 85 °C

Max Cumulative Hours for Intermittent Exposure 800 h

Cold Lead Length 8 m

Table 1/1

Catalog Number	Item Name	Length
159067-000	GM-2X-SA-12	12 m
650854-000	GM-2X-SA-16	16 m
973923-000	GM-2X-SA-20	20 m
838627-000	GM-2X-SA-25	25 m
925956-000	GM-2X-SA-30	30 m
191808-000	GM-2X-SA-5	5 m
106160-000	GM-2X-SA-8	8 m

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.