

## EM2-CM-MAT CONSTANT WATTAGE HEATING MAT



nVent RAYCHEM EM2-CM-MAT are constant output heating mats for fast and effective ramp and access way heating, to prevent snow and ice formation. Pre-defined power and pre-terminated, available in varying fixed lengths.

### FEATURES & BENEFITS

Simple to design: pre-defined 300 W/m<sup>2</sup> power output

Easy to install: pre-terminated mats, in various sizes 1.2 to 12.6 m<sup>2</sup>, each with 4 m power cable

Safe and efficient in operation through advanced energy saving controls

Reliable during long life: 10 year product warranty available, maintenance free

### SPECIFICATIONS

**Heating Cable Technology** Constant Wattage

**Supply Voltage** 220 – 240 V

**Nominal Power Output @ 230V** 300 W/m<sup>2</sup>

**Outer Jacket Material** PVC

**Color** Blue

**Outer Diameter** 7 mm

**Min Installation Temperature** 5 °C

**Conductor Quantity** 2

**Max Continuous Exposure Temperature, Power Off** 65 °C

Cold Lead Length 4 m

Table 1/1

Catalog Number	Item Name	Length	Width
1244-004894	EM2-CM-MAT-16M	16 m	600 mm
1244-004895	EM2-CM-MAT-21M	21 m	600 mm

**North America**

Tel +1.800.545.6258  
Fax +1.800.527.5703  
thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
Fax +32.16.213.604  
thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
Fax +1.713.868.2333  
thermal.info@nvent.com



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
nVent reserves the right to change specifications without notice.