

QTVR SELF-REGULATING HEATING CABLE



nVent RAYCHEM QTVR self-regulating trace heating cables are suitable for freeze protection of large pipes/vessels with high heat loss, and for process temperature maintenance applications without steam-cleaning requirements, up to 225 °F/110 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

FEATURES & BENEFITS

Simplified design for hazardous areas: unconditional T4 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Supply Voltage 200 – 277 V

Area Classification Non-Hazardous; Hazardous

Outer Jacket Material Fluoropolymer

Ground Path Type Braid

Max Maintain or Continuous Exposure Temperature, Power On/Off 110 °C

Max Intermittent Exposure Temperature, Power On/Off 110 °C

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
391991-000	10QTVR2-CT	38 W/m

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
040615-000	15QTVR2-CT	51 W/m
988967-000	20QTVR2-CT	64 W/m

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nvent.com



Our powerful portfolio of brands:
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.
 nVent reserves the right to change specifications without notice.