

Threaded Stud



FEATURES

Pre-cut lengths of threaded rod

SPECIFICATIONS


Quality Class: 4.6
Finish: Electrogalvanized
Material: Steel

Table 1/1

Catalog Number	Article Number	E-Number	Rod Size (RS)	Length (L)
051M10025	400345	3435873	M10	25mm
051M8025	400336	3435867	M8	25mm
051M8040	400337	3435868	M8	40mm
051M10040	400346	3435874	M10	40mm
051M8060	400338	3435869	M8	60mm
051M10060	400347	3435875	M10	60mm
051M8070	593465	3535395	M8	70mm
051M10080	400349	3435876	M10	80mm
051M8080	400340	3435871	M8	80mm
051M10090	593505	3535404	M10	90mm
051M8100	400342	3435872	M8	100mm
051M10100	400351	3435877	M10	100mm

Catalog Number	Article Number	E-Number	Rod Size (RS)	Length (L)
051M10150	593516	3535406	M10	150mm
051M8150	593477	3535398	M8	150mm
051M8120	593476	3535397	M8	120mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

