


920 SERIES



RAYCHEM

DUAL-POINT HEAT-TRACING CONTROL SYSTEM



920*E4FWL*SIS302*SS3102 shown

PRODUCT OVERVIEW

The nVent RAYCHEM 920 is a compact, full-featured, microprocessor-based, dual-point heat-tracing control system. The 920 provides control and monitoring of two independent electrical heat-tracing circuits for both freeze protection and temperature maintenance, and can be set to monitor and alarm for high and low temperature, high and low current, ground-fault level, and voltage on each of its control points. The RAYCHEM 920 controller is available with two output types: an electromechanical relay (EMR) for use in nonhazardous locations and a solid-state relay (SSR) for use in nonhazardous and Class I Div. 2/Zone 2 hazardous locations. Communications modules are available for remote control and configuration, complete with RAYCHEM Supervisor software capability.

Control

The RAYCHEM 920 measures temperatures with 3-wire 100-ohm platinum RTDs connected directly to the unit. Up to two RTDs are supported for each of the two control points. The controller may be used in line-sensing, ambient-sensing, proportional ambient-sensing, and power-limiting modes.

Monitoring

A variety of parameters are measured, including ground fault, temperature, and current to ensure system integrity. The system can be set to periodically check the heating cable for faults, alerting maintenance personnel of a heat-tracing problem.

A dry contact relay is provided for alarm annunciation back to a distributed control system (DCS).

Ground-fault protection

National electrical codes require ground-fault equipment protection on all heat-tracing circuits. The RAYCHEM 920 controllers incorporate the ground-fault sensing, alarm, and trip functionality internally. Heat-tracing circuits equipped with RAYCHEM 920 controllers do not require additional ground-fault detection equipment, simplifying installation and reducing costs.

Installation

The standard RAYCHEM 920 unit comes ready to install right from the box, eliminating the need for custom panel design or field assembly. Custom configurations are also available from the factory to allow the user to tailor the solution to the application.







The TYPE 4X-rated FRP or optional stainless steel enclosures are approved for use in indoor and outdoor locations. Wiring is as simple as connecting the incoming and outgoing power wiring (up to 600 Vac) and an RTD.

The RAYCHEM 920 operator console includes LED displays and function keys that make it easy to use and program. No additional handheld programming devices are needed. Alarm conditions and programming settings are easy to interpret on the full-text front panel. Settings are stored in nonvolatile memory in the event of power failure.

Communications

RAYCHEM 920 units may be networked to a host PC running Windows®-based RAYCHEM Supervisor software for central programming, status review, and alarm annunciation. RAYCHEM 920 units support the Modbus® protocol and may be ordered with an RS-485 communications interface.

GENERAL

Area of use	Nonhazardous locations (EMR versions) Nonhazardous and Division 2 hazardous locations (SSR versions)						
Approvals	<table><tr><td>Nonhazardous locations (SSR and EMR versions)</td><td>Hazardous locations (SSR versions only)</td></tr><tr><td></td><td></td></tr><tr><td></td><td>Class I, Div. 2, Groups A, B, C, D Ex nA IIC T-code: T4 (T3A with optional alarm light)</td></tr></table>	Nonhazardous locations (SSR and EMR versions)	Hazardous locations (SSR versions only)				Class I, Div. 2, Groups A, B, C, D Ex nA IIC T-code: T4 (T3A with optional alarm light)
Nonhazardous locations (SSR and EMR versions)	Hazardous locations (SSR versions only)						
							
	Class I, Div. 2, Groups A, B, C, D Ex nA IIC T-code: T4 (T3A with optional alarm light)						
Supply voltage	100 Vac to 277 Vac, +5% / -10%, 50/60 Hz Common supply for controller and heat-tracing circuit Up to 600 Vac for heat-tracing circuit when controller is powered from a separate circuit or when transformer option is included						


ENCLOSURE

Protection	TYPE 4X
Materials	FRP or optional stainless steel
Ambient operating temperature range	-40°F to 140°F (-40°C to 60°C)
Ambient storage temperature range	-40°F to 185°F (-40°C to 85°C)
Relative humidity	0% to 90%, noncondensing

CONTROL

Relay types	3-pole, mechanical (EMR versions) 1-, 2-, or 3-pole solid-state, normally open (SSR versions)
Voltage, maximum	277 Vac nominal, 50/60 Hz (standard), 600 Vac nominal (optional)
Current, maximum	30 A @ 104°F (40°C) (standard) For ratings at higher ambient temperatures, contact the factory. 60 A @ 104°F (40°C) (optional)
Control algorithms	EMR: Line sensing on/off, proportional ambient SSR: Line sensing on/off, proportional, proportional ambient, power limiting, soft start
Control range	-76°F to 1058°F (-60°C to 570°C)

TYPICAL ENCLOSURE DIMENSIONS



920*E4FWL*SIS302*SS3102 (1 pole model) shown
920*E4FWL*SIS302*SS3202 (2 pole model)

MONITORING (EACH CONTROL POINT)

Temperature	Low alarm range	-76°F to 1058°F (-60°C to 570°C) or OFF
	High alarm range	-76°F to 1058°F (-60°C to 570°C) or OFF
Ground fault	Alarm range	20 mA to 250 mA or OFF
	Trip range	20 mA to 250 mA or OFF
Current	Low alarm range	0.3 A to 100 A or OFF
	High alarm range	0.3 A to 100 A or OFF
	Power limit	3 W to 33 kW
Voltage	Low alarm range	10 V to 330 V or OFF
	High alarm range	10 V to 330 V or OFF
Resistance	Low resistance range	1% to 100% of deviation from nominal
	High resistance range	1% to 250% of deviation from nominal
Autocycle	Diagnostic test interval adjustable from 1 to 240 minutes or 1 to 240 hours	

TEMPERATURE SENSOR INPUTS (EACH CONTROL POINT)

Quantity	Two inputs standard
Types	100 Ω platinum RTD, 3-wire, $\alpha = 0.00385$ ohms/ohm/°C Can be extended with a 3-conductor shielded cable of 20 Ω maximum per conductor 100 Ω Ni-Fe RTD, 2-wire

ALARM OUTPUTS

Dry contact relay	Pilot duty only, 48 Vac/dc, 500 mA maximum, 10 VA maximum resistive switching
-------------------	---

Note: Output is configurable as “open on alarm” or “close on alarm”

PROGRAMMING AND SETTING

Method	Programmable keypad or communications
Units	°F or °C
Digital display (using optional operator console)	Actual temperature, control temperature, heater current, voltage, resistance, ground fault, programming parameter values, alarm values
LEDs	Power on, heater(s) on, alarm conditions, receive/transmit data (standard) Current mode, heater(s) on, alarm conditions, receive/transmit data (using optional operator console)
Memory	Nonvolatile, restored after power loss, checksum data checking
Stored parameters (measured)	Minimum and maximum process temperature, maximum ground-fault current, maximum heater current, power accumulator, contactor cycle count, time in use
Alarm conditions	Low/high temperature, low/high current, low/high voltage, low/high resistance Ground-fault alarm, trip RTD failure, loss of programmed values, or EMR or SSR failure
Other	Multi-language support Password protection

CONNECTION TERMINALS

Power supply input	Screw terminals, 22–8 AWG (30 A versions), 14–6 AWG (60 A versions)
Heating cable output	Screw terminals, 22–8 AWG (30 A versions), 14–6 AWG (60 A versions)
Ground	14–4 AWG ground bar
RTD/alarm/communications	28–12 AWG spring clamp terminals

MOUNTING

2 point FRP enclosure	Surface mounting with four fixing holes on 15.1 in x 10 in (384 mm x 254 mm) centers Hole diameter: 0.31 in (8 mm)
4 point FRP enclosure	Surface mounting with four fixing holes on 17.1 in x 12 in (435 mm x 305 mm) centers Hole diameter: 0.31 in (8 mm)
8 point FRP enclosure	Surface mounting with four fixing holes on 31.3 in x 21.9 in (795 mm x 556 mm) centers Hole diameter: 0.40 in (10 mm)
20 point FRP enclosure	Surface mounting with four fixing holes on 41.2 in x 30.2 in (1047 mm x 767 mm) centers Hole diameter: 0.40 in (10 mm)

COMMUNICATIONS (OPTIONAL)

Protocol	Modbus RTU or ASCII / HTCBus
Topology	Multidrop, daisy chain
Cable	Single shielded twisted pair, 26 AWG or larger
Length	1.7 miles (2.7 km) maximum @ 9600 baud
Quantity	Up to 32 devices without repeater
Address	Programmable

ORDERING DETAILS

RAYCHEM 920 Series Dual-point Heat-Tracing Control System

Description	Catalog number	Part number	Weight/lbs
RAYCHEM 920 controller—2 Pt in a 14" x 12" x 8" FRP enclosure with window and quick-release latches, control module, and operator console. 1P 30 A 277 V SSR/pt. Controls two circuits, each with a 1-pole solid-state relay. (Approved for Class I, Div. 2 locations)	920*E4FWL*SIS302*SS3102*HTC*CON	10160-010	27
RAYCHEM 920 controller—2 Pt in a 14" x 12" x 8" FRP enclosure with window and quick-release latches, control module, and operator console. Includes an isolated 2-wire RS-485 communication option. 1P 30 A 277 V SSR/pt. Controls two circuits, each with a 1-pole solid-state relay. (Approved for Class I, Div. 2 locations)	920*E4FWL*SIS302*SS3102*HTC485*CON	10160-011	27
RAYCHEM 920 controller—2 Pt in a 14" x 12" x 8" FRP enclosure with window and quick-release latches, control module, and operator console. 2P 30 A 277 V SSR/pt. Controls two circuits, each with a 2-pole solid-state relay. (Approved for Class I, Div. 2 locations)	920*E4FWL*SIS302*SS3202*HTC*CON	10160-012	32
RAYCHEM 920 controller—2 Pt in a 14" x 12" x 8" FRP enclosure with window and quick-release latches, control module, and operator console. Includes an isolated 2-wire RS-485 communication option. 2P 30 A 277 V SSR/pt. Controls two circuits, each with a 2-pole solid-state relay. (Approved for Class I, Div. 2, locations)	920*E4FWL*SIS302*SS3202*HTC485*CON	10160-013	32
RAYCHEM-Supervisor Software	Available for download at nVent.com/RAYCHEM		

ORDERING DETAILS

RAYCHEM 920 Series Dual-point Heat-Tracing Control System


Description	Catalog number	Part number	Weight/lbs
CONTROL MODULES—Requires one for every two control points			
RAYCHEM 920 controller —Control module only (No communications options installed)	920HTC	10260-001	1
RAYCHEM 920 controller —Control module with an isolated 2-wire RS-485 communication option installed	920HTC*485	10260-004	1
OPERATOR CONSOLE—Requires at least one per panel			
RAYCHEM 920 controller —Operator console	920CON	10260-005	1
RTD Sensors			
100-ohm platinum RTD with 10 foot stainless-steel corrugated sheath	RTD10CS	RTD10CS	1.0
RTD, ambient, cable style	RTD-200	254741	0.1
C1D1 RTD, -100°F to 900°F, pipe mounted	RTD7AL	RTD7AL	2.0
RTD, -100°F to 900°F, pipe mounted	RTD4AL	RTD4AL	1.2

ORDERING DETAILS

RAYCHEM 920 Series Dual-point Heat-Tracing Control System

Description	Catalog number	Part number	Weight/lbs
-------------	----------------	-------------	------------

920 * Enclosure * Sensing Components * Output Devices * Options * Controller Parts * Console



North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.603
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER