

# QTVR SELF-REGULATING HEATING CABLE



nVent RAYCHEM QTVR self-regulating trace heating cables are suitable for freeze protection of large pipes/vessels with high heat loss, and for process temperature maintenance applications without steam-cleaning requirements, up to 225 °F/110 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

## FEATURES & BENEFITS

Simplified design for hazardous areas: unconditional T4 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIONS

**Supply Voltage** 200 – 277 V

**Area Classification** Non-Hazardous; Hazardous

**Outer Jacket Material** Fluoropolymer

**Ground Path Type** Braid

**Max Maintain or Continuous Exposure Temperature, Power On/Off** 110 °C

**Max Intermittent Exposure Temperature, Power On/Off** 110 °C

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
391991-000	10QTVR2-CT	38 W/m

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
040615-000	15QTVR2-CT	51 W/m
988967-000	20QTVR2-CT	64 W/m

**North America**

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
 thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
 Fax +32.16.213.604  
 thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
 cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
 thermal.info@nvent.com



Our powerful portfolio of brands:  
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
 nVent reserves the right to change specifications without notice.