

## MI SERIES CUNI HDC/HDF HEATING CABLE



nVent RAYCHEM HDF/HDC mineral insulated (MI) series resistance trace heating cables provide freeze protection and process temperature maintenance, with continuous exposure temperatures to 400 °C and typical power outputs up to 70 W/m. The high nickel content provides high corrosion resistance, especially in seawater environments. Approved for use in hazardous areas. Available 'fast track' as configured heating units and in low resistances, for long pipeline heating.

### FEATURES & BENEFITS

Reduced total installed cost

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track/expedited service for configured heating units for eligible designs

Standard 400 °C continuous withstand temperature, with brazed weld technology

High corrosion resistance, especially in seawater environments

### SPECIFICATIONS

**Supply Voltage** 0 – 500 V

**Max Power Output** 70 W/m

**Max Continuous Exposure Temperature, Power Off** 400 °C

**Insulation Material** Magnesium Oxide

**Sheath Material** Cupro-Nickel

**Area Classification** Non-Hazardous; Hazardous

**Min Installation Temperature** -60 °C

Table 1/1

Catalog Number	Nominal Resistance @ 20°C	Outer Diameter
HDF1M1000	1000 Ω/km	3.4 mm
HDC1M11	11 Ω/km	4.9 mm
HDF1M160	160 Ω/km	4.9 mm
HDF1M1600	1600 Ω/km	3.2 mm
HDC1M17	17 Ω/km	4.6 mm
HDC1M25	25 Ω/km	3.7 mm
HDF1M250	250 Ω/km	4.4 mm
HDC1M4	4 Ω/km	5.9 mm
HDC1M40	40 Ω/km	3.4 mm
HDF1M400	400 Ω/km	4 mm
HDC1M63	63 Ω/km	3.2 mm
HDF1M630	630 Ω/km	3.7 mm
HDC1M7	7 Ω/km	5.3 mm

**North America**

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
 thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
 Fax +32.16.213.604  
 thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
 cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
 thermal.info@nvent.com



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**