

# BTV SELF-REGULATING HEATING CABLE



nVent RAYCHEM BTV self-regulating trace heating cables provide freeze protection and process temperature maintenance, up to 150 °F/65 °C, of pipes/vessels without steam cleaning requirements. They withstand intermittent exposure to 185 °F/85 °C and are hazardous area approved. The polyolefin outer jacket (-CR) is suitable for mild inorganic solutions. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

## FEATURES & BENEFITS

Simplified design in hazardous area: unconditional T6 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIONS

**Supply Voltage** 200 – 277 V

**Area Classification** Non-Hazardous; Hazardous

**Ground Path Type** Braid

**Outer Jacket Material** Fluoropolymer

**Max Maintain or Continuous Exposure Temperature, Power On/Off** 65 °C

**Max Intermittent Exposure Temperature, Power On/Off** 85 °C

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
567513-000	10BTV2-CT	29 W/m
469145-000	3BTV2-CT	9 W/m

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
487509-000	5BTV2-CT	16 W/m
008633-000	8BTV2-CT	25 W/m

**Supply Voltage** 200 – 277 V

**Area Classification** Non-Hazardous; Hazardous

**Ground Path Type** Braid

**Outer Jacket Material** Modified Polyolefin

**Max Maintain or Continuous Exposure Temperature, Power On/Off** 65 °C

**Max Intermittent Exposure Temperature, Power On/Off** 85 °C

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
677245-000	10BTV2-CR	29 W/m
914279-000	3BTV2-CR	9 W/m
414809-000	5BTV2-CR	16 W/m
479821-000	8BTV2-CR	25 W/m

**North America**

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
 thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
 Fax +32.16.213.604  
 thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
 cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
 thermal.info@nvent.com



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**