



RAYCHEM

FHT CONSTANT WATTAGE PARALLEL HEATING CABLE



nVent RAYCHEM FHT constant wattage parallel trace heating cables provide freeze protection and process temperature maintenance, up to 230 °C. They can withstand routine steam purges and intermittent exposure to 260 °C, available in 230 and 400 V and approved for use in hazardous areas. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

FEATURES & BENEFITS

Fast installation: round geometry, cut-to-length, meter markings, user-friendly connection kits

Safe and efficient in operation, energy saving technology

Extended circuit lengths, available in 230 V and 400 V versions

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Max Continuous Exposure Temperature, Power Off 260 °C

Outer Jacket Material PFA

Ground Path Type Braid

Area Classification Hazardous

Min Installation Temperature -60 °C

Min Bending Radius 25 mm

Min Clearance 50 mm

Outer Diameter 7.5 mm

Nominal Cold Lead/Heating Zone Length 1.5 m

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 230V	Max Power Output @ 230V
1244-006060	10FHT2-CT	10 W/m	12.7 W/m
1244-006061	20FHT2-CT	20 W/m	25.5 W/m
1244-006062	30FHT2-CT	30 W/m	38.2 W/m
1244-006063	40FHT2-CT	40 W/m	51 W/m

Max Continuous Exposure Temperature, Power Off 260 °C

Outer Jacket Material PFA

Ground Path Type Braid

Area Classification Hazardous

Min Installation Temperature -60 °C

Min Bending Radius 25 mm

Min Clearance 50 mm

Outer Diameter 7.5 mm

Nominal Cold Lead/Heating Zone Length 2.5 m

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 400V	Max Power Output @ 400V
1244-006064	10FHT4-CT	10 W/m	12.7 W/m
1244-006065	20FHT4-CT	20 W/m	25.5 W/m
1244-006066	30FHT4-CT	30 W/m	38.2 W/m

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nvent.com



Our powerful portfolio of brands:
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.