


# Coding Strip



The coding is mounted on the side of a connector. With the Coding only the coded board can fit into the right slot.

## CERTIFICATIONS



## FEATURES

Mechanical coding prevents a PSU being fitted on the wrong slot, space requirement 4 HP

Female strip (item 2), fitted on PSU

Coding strip (item 1) mounts on the Z/horizontal rail

Placement of coding pins (item 3) in the coding strip (item 1)

Removal of studs at the appropriate place in the female strip

With 2 coding pins there are 66 coding possibilities

## SPECIFICATIONS

|                      |                            |
|----------------------|----------------------------|
| <b>Works With:</b>   | 19" Power Supplies         |
| <b>Type:</b>         | Coding Strip               |
| <b>Product Type:</b> | Coding/Keying Indicator    |
| <b>Material:</b>     | Polybutylene Terephthalate |

Table 1/1

| Catalog Number | Package Quantity | Number of Pins | Certifications |
|----------------|------------------|----------------|----------------|
| 60800-123      | 1                | (1) 2          | RoHS           |
| 60800-122      | 1                |                |                |

ADDITIONAL PRODUCT DETAILS

Coding strip; Coding block; Keying strip

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE