

# Socket Strip, SCHUKO

## Data Solutions



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

### CERTIFICATIONS



### FEATURES

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

### SPECIFICATIONS

|                      |                     |
|----------------------|---------------------|
| <b>Material:</b>     | Aluminum; Polyamide |
| <b>Color:</b>        | Grey                |
| <b>Product Type:</b> | Socket Strip        |

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Function                                         | Package Quantity |
|----------------|-------------|-----------------|------------------|------------|--------------------------------------------------|------------------|
| 60110-207      | SCHUKO      | 12              | Yes              | 230V       |                                                  | 1                |
| 60110-202      | SCHUKO      | 9               | No               | 230V       |                                                  | 1                |
| 60110-266      | SCHUKO      | 6               | No               | 230V       | Transient Protection, Mains Suppression Filter   | 1                |
| 60110-203      | SCHUKO      | 12              | No               | 230V       |                                                  | 1                |
| 60110-204      | SCHUKO      | 15              | No               | 230V       |                                                  | 1                |
| 60110-205      | SCHUKO      | 19              | No               | 230V       |                                                  | 1                |
| 60110-217      | SCHUKO      | 6               | No               | 230V       | Fault Current Protection, Overcurrent Protection | 1                |
| 60110-201      | SCHUKO      | 4               | No               | 230V       |                                                  | 1                |
| 60110-206      | SCHUKO      | 8               | Yes              | 230V       |                                                  | 1                |
| 60110-208      | SCHUKO      | 15              | Yes              | 230V       |                                                  | 1                |
| 60110-216      | SCHUKO      | 6               | No               | 230V       | Fault Current Protection                         | 1                |
| 60110-209      | SCHUKO      | 19              | Yes              | 230V       |                                                  | 1                |
| 60110-210      | SCHUKO      | 8               | No               | 230V       | Transient Protection                             | 1                |
| 60110-211      | SCHUKO      | 9               | No               | 230V       | Transient Protection                             | 1                |
| 60110-214      | SCHUKO      | 7               | No               | 230V       | Mains Suppression Filter                         | 1                |
| 60110-200      | SCHUKO      | 3               | No               | 230V       |                                                  | 1                |
| 60110-212      | SCHUKO      | 6               | No               | 230V       | Overcurrent Protection                           | 1                |

Table 2/2

| Catalog Number | Depth | Finish   | Length  |
|----------------|-------|----------|---------|
| 60110-207      | 44mm  | Anodized | 947.5mm |
| 60110-202      | 44mm  | Anodized | 438.5mm |
| 60110-266      | 44mm  | Anodized | 438.5mm |
| 60110-203      | 44mm  | Anodized | 947.5mm |
| 60110-204      | 44mm  | Anodized | 1202mm  |

| Catalog Number | Depth | Finish   | Length  |
|----------------|-------|----------|---------|
| 60110-205      | 44mm  | Anodized | 1753mm  |
| 60110-217      | 88mm  | Anodized | 438.5mm |
| 60110-201      | 44mm  | Anodized | 210mm   |
| 60110-206      | 44mm  | Anodized | 438.5mm |
| 60110-208      | 44mm  | Anodized | 1202mm  |
| 60110-216      | 88mm  | Anodized | 438.5mm |
| 60110-209      | 44mm  | Anodized | 1753mm  |
| 60110-210      | 44mm  | Anodized | 438.5mm |
| 60110-211      | 44mm  | Anodized | 947.5mm |
| 60110-214      | 44mm  | Anodized | 438.5mm |
| 60110-200      | 44mm  | Anodized | 184mm   |
| 60110-212      | 75mm  | Anodized | 438.5mm |

## ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**