

## MODULAR JUNCTION BOX



nVent RAYCHEM JBU-100 is a modular junction box used to connect power to up to three nVent RAYCHEM BTV, QTVR, XTV, KTV or VPL industrial parallel heating cables. Offered in two versions, customized for local installation practices. All kits are also available with a light for power indication.

### FEATURES & BENEFITS

---

Simple and fast to install, spacious boxes with front access, captive lid screws and robust spring type terminals for secure fixing

Part of a modular component system, providing maximum flexibility

One range for all nVent RAYCHEM industrial parallel heating cables

Simplified design in hazardous area, integral part of system approval

Cold-applied: core sealing boot with non-curing sealant; no heat gun, no hot work permit needed

Reliable during long life: 10 year extended product warranty available, maintenance free

### SPECIFICATIONS

---

**Material** Glass Fiber Reinforced Polymer

**Mounting** Wall/Support Bracket Mounted

**IP Rating** IP66

**Inlet Type** Cable

**Inlet Quantity** 4

**Cover Attachment** Screwed

**For Ex-Zone Gas** 1, 2

**For Ex-Zone Dust** 21, 22

**Max Conductor Cross Section** 10 mm<sup>2</sup>

**Halogen Free** Yes

**Connection Clamp Quantity** 6

**Area Classification** Non-Hazardous; Hazardous

Table 1/2

Catalog Number	Item Name	Ambient Temperature	Height	Depth	Width	Light Indication Included
243948-000	JBU-100-EP	-55 to 56 °C	160 mm	90 mm	160 mm	No
113974-000	JBU-100-L-EP	-40 to 40 °C	160 mm	90 mm	160 mm	Yes
069262-000	JBU-100-L-E	-40 to 40 °C	160 mm	90 mm	160 mm	Yes
051976-000	JBU-100-E	-55 to 56 °C	160 mm	90 mm	160 mm	No

Table 2/2

Catalog Number	Item Name	Earth Plate Included	Below Insulation
243948-000	JBU-100-EP	Yes	No
113974-000	JBU-100-L-EP	Yes	No
069262-000	JBU-100-L-E	No	No
051976-000	JBU-100-E	No	No

Localized versions may exist with limited approvals and different part numbers. Contact your local sales representative.

**North America**

Tel +1.800.545.6258  
Fax +1.800.527.5703  
thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
Fax +32.16.213.604  
thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
Fax +1.713.868.2333  
thermal.info@nvent.com



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
nVent reserves the right to change specifications without notice.