

AT-TS SURFACE SENSING THERMOSTAT



nVent RAYCHEM AT-TS Thermostats are electronic line or ambient sensing thermostats for self-regulating heating cables in pipe freeze protection or temperature maintenance applications.

FEATURES & BENEFITS

Energy saving, line-sensing or ambient electronic control thermostat.

Adjustable: $-5\text{ }^{\circ}\text{C}$ to $+15\text{ }^{\circ}\text{C}$ (AT-TS-13), $0\text{ }^{\circ}\text{C}$ to $+120\text{ }^{\circ}\text{C}$ (AT-TS-14)

Direct switching of heating cables, maximum current 16 A, 250 VAC

Simple and fast to install

Easy to use: LEDs indicate when cables are energized or when temperature sensor is defective

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIONS

IP Rating IP65

Height 120 mm

Width 122 mm

Depth 55 mm

Table 1/1

Catalog Number	Item Name	Temperature Control Range
648945-000	AT-TS-14	0 – 120 $^{\circ}\text{C}$

Catalog Number	Item Name	Temperature Control Range
728129-000	AT-TS-13	-5 to 15 °C

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nvent.com



Our powerful portfolio of brands:
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.
 nVent reserves the right to change specifications without notice.