

FROSTOP SELF-REGULATING HEATING CABLE

nVent RAYCHEM Frostop self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection and roof and gutter de-icing.



FEATURES & BENEFITS

Simple to design

Easy to install: cut to length, meter marks

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Outer Jacket Material Modified Polyolefin

Color Black

Ground Path Type Braid

Min Installation Temperature -18 °C

Table 1/2

| Catalog Number | Item Name | Supply Voltage | Nominal Voltage | Nominal Power Output @ 5°C, 230V | Max Circuit Length | Nominal Width |
|----------------|----------------------|----------------|-----------------|----------------------------------|--------------------|---------------|
| 559303-000 | FROSTOP-BLACK-RANDOM | 220 – 240 V | 220; 230; 240 V | 18 W/m | 80 m | 10.5 mm |

Table 2/2

| Catalog Number | Item Name | Nominal Height | Conductor Material | Min Bending Radius | Nominal Thickness |
|----------------|----------------------|----------------|----------------------|--------------------|-------------------|
| 559303-000 | FROSTOP-BLACK-RANDOM | 5.5 mm | Nickel-Plated Copper | 10 mm | 5.5 mm |

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.