

# BSA SELF-REGULATING HEATING CABLE



nVent RAYCHEM BSA self-regulating trace heating cables are an ideal solution for freeze protection of pipes and vessels and for process temperature maintenance, in non-hazardous industrial locations, without steam-cleaning requirement. They maintain process temperatures up to 65°C and can withstand intermittent exposure temperatures up to 85°C. BSA heating cables use the same heating core and polyolefin inner jacket as the BTV. The earth path consists of an aluminum foil wrap and metallic drain wires, providing 100% electrical protection coverage. The polyolefin outer jacket is suitable for mild inorganic solutions and provides excellent protection.

## FEATURES & BENEFITS

Foil wrap /drain-wire construction and modified polyolefin jackets provide a highly flexible cable

The unique construction allows stripping the jackets in no time, for fast connection

100% electrical earth path coverage for ultimate safety

Reliable long life performance with a 10 year product warranty available

## SPECIFICATIONS

**Supply Voltage** 0 – 230 V

**Outer Jacket Material** Polyolefin

**Ground Path Type** Foil and Drainwire

**Area Classification** Non-Hazardous

**Conductor Material** Nickel-Plated Copper

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V	Max Circuit Length	Nominal Width	Nominal Thickness
P000002271	3BSA2-DR	10 W/m	150 m	13.7 mm	6.2 mm

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V	Max Circuit Length	Nominal Width	Nominal Thickness
P000002272	7BSA2-DR	23 W/m	120 m	13.7 mm	6.2 mm

**North America**

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
 thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
 Fax +32.16.213.604  
 thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
 cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
 thermal.info@nvent.com



Our powerful portfolio of brands:  
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**