

## EM4-CW CONSTANT WATTAGE CABLE KIT



nVent RAYCHEM EM4-CW is a constant output trace heating cable for simple, fast and effective ramp and access way heating to prevent snow and ice formation. It is designed for applications where a 3 phase (400 V) supply is available. Pre-terminated.

### FEATURES & BENEFITS

Simple to design: variable power output dependent upon cable spacing, up to 300 W/m<sup>2</sup>, variety of sizes available to meet project requirements

Easy to install: flexible, excellent for irregular shaped areas, pre-terminated

Safe and efficient in operation through advanced energy saving controls

Reliable during long life: 10 year product warranty available, maintenance free

### SPECIFICATIONS

**Heating Cable Technology** Constant Wattage

**Nominal Voltage** 400 V

**Nominal Power Output @ 400V** 25 W/m

**Outer Jacket Material** PVC

**Color** Blue

**Ground Path Type** Braid

**Area Classification** Non-Hazardous

**Min Installation Temperature** 5 °C

**Max Continuous Exposure Temperature, Power Off** 65 °C

**Cold Lead Length** 4 m

**Min Bending Radius** 50 mm

Table 1/1				
Catalog Number	Item Name	Nominal Width	Nominal Height	Length
1244-005191	EM4-CW-121M	8.9 mm	5.5 mm	121 m
1244-005194	EM4-CW-172M	8.9 mm	5.5 mm	172 m
1244-005196	EM4-CW-210M	8.9 mm	5.5 mm	210 m
1244-005198	EM4-CW-250M	8.9 mm	5.5 mm	250 m
1244-005182	EM4-CW-26M	8.9 mm	5.5 mm	26 m
1244-005184	EM4-CW-35M	8.9 mm	5.5 mm	35 m
1244-005188	EM4-CW-62M	8.9 mm	5.5 mm	62 m

The heating cable should be installed on a stable subsurface. In suspended structures the substratum may consist of finished slabs, pre-stressed concrete or a suspended structure with poured concrete. The heating cables can be laid on all subsurfaces including reinforcement grids/bars. In the case of poured concrete, it should be ensured that the surface is smooth and all sharp objects are removed. Ramps on a solid substratum do not require any additional thermal insulation. Appropriate preparations should be made for installing the temperature and moisture sensor.

**North America**

Tel +1.800.545.6258  
Fax +1.800.527.5703  
thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
Fax +32.16.213.604  
thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
Fax +1.713.868.2333  
thermal.info@nvent.com



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
nVent reserves the right to change specifications without notice.