

MI SERIES CUNI HDC/HDF HEATING CABLE



nVent RAYCHEM HDF/HDC mineral insulated (MI) series resistance trace heating cables provide freeze protection and process temperature maintenance, with continuous exposure temperatures to 400 °C and typical power outputs up to 70 W/m. The high nickel content provides high corrosion resistance, especially in seawater environments. Approved for use in hazardous areas. Available 'fast track' as configured heating units and in low resistances, for long pipeline heating.

FEATURES & BENEFITS

Reduced total installed cost

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track/expedited service for configured heating units for eligible designs

Standard 400 °C continuous withstand temperature, with brazed weld technology

High corrosion resistance, especially in seawater environments

SPECIFICATIONS

Supply Voltage 0 – 500 V

Max Power Output 70 W/m

Max Continuous Exposure Temperature, Power Off 400 °C

Insulation Material Magnesium Oxide

Sheath Material Cupro-Nickel

Area Classification Non-Hazardous; Hazardous

Min Installation Temperature -60 °C

Table 1/1

Catalog Number	Nominal Resistance @ 20°C	Outer Diameter
HDF1M1000	1000 Ω/km	3.4 mm
HDC1M11	11 Ω/km	4.9 mm
HDF1M160	160 Ω/km	4.9 mm
HDF1M1600	1600 Ω/km	3.2 mm
HDC1M17	17 Ω/km	4.6 mm
HDC1M25	25 Ω/km	3.7 mm
HDF1M250	250 Ω/km	4.4 mm
HDC1M4	4 Ω/km	5.9 mm
HDC1M40	40 Ω/km	3.4 mm
HDF1M400	400 Ω/km	4 mm
HDC1M63	63 Ω/km	3.2 mm
HDF1M630	630 Ω/km	3.7 mm
HDC1M7	7 Ω/km	5.3 mm

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER