

XTV SELF-REGULATING HEATING CABLE



nVent RAYCHEM XTV self-regulating trace heating cables are mainly used for freeze protection of pipes and vessels that require steam cleaning and process temperature maintenance, up to 250 °F/121 °C. They withstand intermittent exposure to 482 °F/250 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

FEATURES & BENEFITS

Simplified design in hazardous area: T2 and T3-T6 based on systems approach

Longer circuit lengths due to larger cross section conductors

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Supply Voltage 200 – 277 V

Area Classification Non-Hazardous; Hazardous

Outer Jacket Material High Temperature Fluoropolymer

Ground Path Type Braid

Max Maintain or Continuous Exposure Temperature, Power On 121 °C

Max Intermittent Exposure Temperature, Power On/Off 250 °C

Max Cumulative Hours for Intermittent Exposure 1000 h

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
----------------	-----------	-----------------------------------

P000001667	4XTV2-CT-T3	12 W/m
P000001670	8XTV2-CT-T3	25 W/m
P000001673	12XTV2-CT-T3	38 W/m
P000001675	15XTV2-CT-T3	47 W/m
P000001677	20XTV2-CT-T2	63 W/m

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nvent.com



Our powerful portfolio of brands:
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.
 nVent reserves the right to change specifications without notice.