

## ICESTOP SELF-REGULATING HEATING CABLE



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

### FEATURES & BENEFITS

---

Simple to design

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

GM-2XT for bitumen roofs

### SPECIFICATIONS

---

**Supply Voltage** 208 – 240 V

**Color** Black

**Nominal Width** 14 mm

**Nominal Thickness** 6 mm

**Ground Path Type** Braid

**Min Installation Temperature** -18 °C

**Conductor Material** Nickel-Plated Copper

**Nominal Cable Weight** 130 g/m

Table 1/1

Catalog Number	Item Name	Nominal Power Output, In Air @ 0°C, 230V	Nominal Power Output, In Ice Water @ 0°C, 230V	Outer Jacket Material
446105-000	GM-2X	18 W/m	36 W/m	Modified Polyolefin
092961-000	GM-2XT	18 W/m	36 W/m	Fluoropolymer

**North America**

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East, Africa**

Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.