

# QTVR SELF-REGULATING HEATING CABLE



nVent RAYCHEM QTVR self-regulating trace heating cables are suitable for freeze protection of large pipes/vessels with high heat loss, and for process temperature maintenance applications without steam-cleaning requirements, up to 225 °F/110 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

## FEATURES & BENEFITS

Simplified design for hazardous areas: unconditional T4 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIONS

**Supply Voltage** 200 – 277 V

**Area Classification** Non-Hazardous; Hazardous

**Outer Jacket Material** Fluoropolymer

**Ground Path Type** Braid

**Max Maintain or Continuous Exposure Temperature, Power On/Off** 110 °C

**Max Intermittent Exposure Temperature, Power On/Off** 110 °C

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
391991-000	10QTVR2-CT	38 W/m
040615-000	15QTVR2-CT	51 W/m

Catalog Number	Item Name	Nominal Power Output @ 10°C, 230V
988967-000	20QTVR2-CT	64 W/m

**North America**

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
 thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
 Fax +32.16.213.604  
 thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
 cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
 thermal.info@nvent.com



Our powerful portfolio of brands:  
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**