


## XL-TRACE SELF-REGULATING HEATING CABLE



nVent RAYCHEM XL-Trace self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection and flow maintenance of grease waste lines (above and below ground) and fuel lines (above ground).

### FEATURES & BENEFITS

Simple to design

Easy to install: cut to length, meter marks, fast RayClic cold connection system

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no cable overheating possible, suitable for plastic pipes

Reliable during long life: 10 year extended product warranty available, maintenance free

### SPECIFICATIONS

**Supply Voltage** 208 – 277 V

**Ground Path Type** Braid

**Min Installation Temperature** -18 °C

Table 1/1

Catalog Number	Item Name	Outer Jacket Material	Max Circuit Length	Max Continuous Exposure Temperature, Power Off
858122-000	5XL2-CR	Modified Polyolefin	149 m	65 °C
779713-000	8XL2-CR	Modified Polyolefin	119 m	65 °C

**Supply Voltage** 100 – 120 V

**Ground Path Type** Braid

**Min Installation Temperature** -18 °C

Table 1/1

Catalog Number	Item Name	Outer Jacket Material	Max Continuous Exposure Temperature, Power Off
869218-000	5XL1-CT	Fluoropolymer	65 °C

**North America**

Tel +1.800.545.6258  
Fax +1.800.527.5703  
thermal.info@nvent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
Fax +32.16.213.604  
thermal.info@nvent.com

**Asia Pacific**

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
cn.thermal.info@nvent.com

**Latin America**

Tel +1.713.868.4800  
Fax +1.713.868.2333  
thermal.info@nvent.com



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
nVent reserves the right to change specifications without notice.