

NGC-30 SERIES, STANDARD CONTROL PANEL

nVent RAYCHEM NGC-30 Series - Controller Panel is a range of multi-circuit electronic control, monitoring and power distribution panels for process temperature maintenance and pipe freeze protection applications. Each User Interface Terminal can control up to 260 circuits with multiple networked panels.

FEATURES & BENEFITS

Central status overview and access to all parameters of the entire heat tracing installation through the touch screen user interface terminal, reduces training time and provides simple and easy navigation for maintenance and operations personnel

Significant cost savings through distributed architecture and reduced RTD wiring

SPECIFICATIONS

Voltage Rating 120 – 208 V

Operating Temperature -25 to 60 °C

Table 1/1			
Catalog Number	Item Name	Circuit Breaker Quantity	Z-Purge
10721-010	NGC30-S-20	20	No
10721-013	NGC30-S-20-P	20	Yes
10721-011	NGC30-S-30	30	No
10721-014	NGC30-S-30-P	30	Yes
10721-012	NGC30-S-40	40	No
10721-015	NGC30-S-40-P	40	Yes

Voltage Rating 277 – 480 V

Operating Temperature -25 to 60 °C

Table 1/1			
Catalog Number	Item Name	Circuit Breaker Quantity	Z-Purge

10721-016	NGC30-S-20-4	20	No
10721-019	NGC30-S-20-4-P	20	Yes
10721-017	NGC30-S-30-4	30	No
10721-020	NGC30-S-30-4-P	30	Yes
10721-018	NGC30-S-40-4	40	No
10721-021	NGC30-S-40-4-P	40	Yes

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER