

Single Pole Distribution Block

Data Solutions



CERTIFICATIONS



CARACTERISTICAS

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

95% fill ratio

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

ESPECIFICAÇÕES

Acabamento: Tinned

Table 1/2						
Número de catálogo	Número do artigo	Max Current Rating, IEC	Max Current Rating, UL/CSA	Line Side Connection	Copy of Copy of Output Connection	Material
UDJ-125A	569020	125A	150A	Cable	7 Cables	Copper, Termoplástico
UDF6C500AL	569202	500A	475A	Flat Conductor	6 Cables	Aluminio, Termoplástico
UD6C500AL	569201	500A	380A	Cable	6 Cables	Aluminio, Termoplástico
UD2C9C1250AL	569209	1250A	950A	2 Cables	9 Cables	Aluminio, Termoplástico
UD-400212AL	569251	400A	400A	2 Cables	12 Cables	Aluminio, Termoplástico
UD2C12C1000AL	569207	1000A	760A	2 Cables	12 Cables	Aluminio, Termoplástico
UD2C12C630AL	569205	630A	670A	2 Cables	12 Cables	Aluminio, Termoplástico
UD-400212CU	569051	400A	400A	2 Cables	12 Cables	Copper, Termoplástico
UDJ-160A	569030	160A	200A	Cable	7 Cables	Copper, Termoplástico
UDF9C1000AL	569210	1000A	840A	Flat Conductor	9 Cables	Aluminio, Termoplástico
UDF-250A	569041	250A	255A	Flat Conductor	6 Cables	Copper, Termoplástico
UD-80A	569010	80A	85A	Cable	6 Cables	Copper, Termoplástico
UD9C630AL	569203	630A	420A	Cable	9 Cables	Aluminio, Termoplástico
UDF9C500AL	569204	500A	490A	Flat Conductor	9 Cables	Aluminio, Termoplástico
UD-400112CU	569052	400A	335A	Cable	12 Cables	Copper, Termoplástico
UD-400112AL	569252	400A	335A	Cable	12 Cables	Aluminio, Termoplástico
UDF-500A	569060	500A	335A	Flat Conductor	11 Cables	Copper, Termoplástico
UD-400A	569050	400A	335A	Cable	11 Cables	Copper, Termoplástico

Número de catálogo	Número do artigo	Max Current Rating, IEC	Max Current Rating, UL/CSA	Line Side Connection	Copy of Copyof Output Connection	Material
UD-250A	569040	250A	255A	Cable	11 Cables	Copper, Termoplástico
UDF12C800AL	569208	800A	670A	Flat Conductor	12 Cables	Aluminio, Termoplástico
UDF12C500AL	569206	500A	500A	Flat Conductor	12 Cables	Aluminio, Termoplástico

Table 2/2

Número de catálogo	Número do artigo	Line Side Max Conductor Size, IEC	Load Side Max Conductor Size, IEC	Max Working Voltage, IEC (Ui)	Max Working Voltage, UL (Vin)	Certifications
UDJ-125A	569020	35 mm ²	16 mm ²	1000	600	RoHS, cUR, CSA, CE, ERIFLEX UD, UR
UDF6C500AL	569202	100 mm ²	50 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UD6C500AL	569201	240 mm ²	50 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UD2C9C1250AL	569209	400 mm ²	95 mm ²	1000, 1500	1000	UL, cUL, QPQS7.E49727 6
UD-400212AL	569251	95 mm ²	10 mm ²	1000, 1500	1000	cUR, CSA, RoHS, UR, CE, ERIFLEX UD
UD2C12C1000AL	569207	240 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UD2C12C630AL	569205	185 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UD-400212CU	569051	95 mm ²	10 mm ²	1000, 1500	1000	RoHS, cUR, CSA, CE, ERIFLEX UD, UR
UDJ-160A	569030	70 mm ²	16 mm ²	1000	600	CE, ERIFLEX UD, UR, RoHS, cUR, CSA
UDF9C1000AL	569210	240 mm ²	95 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL

Número de catálogo	Número do artigo	Line Side Max ConductorSize, IEC	Load Side Max ConductorSize, IEC	Max Working Voltage, IEC (Ui)	Max Working Voltage, UL (Vin)	Certifications
UDF-250A	569041	70 mm ²	16 mm ²	1000	600	RoHS, UR, CE, ERIFLEX UD, cUR
UD-80A	569010	16 mm ²	16 mm ²	1000	600	cUR, CSA, RoHS, UR, CE, ERIFLEX UD
UD9C630AL	569203	300 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL
UDF9C500AL	569204	100 mm ²	25 mm ²	1000, 1500	1000	UL, cUL, QPQS7.E49727 6
UD-400112CU	569052	185 mm ²	10 mm ²	1000, 1500	1000	UR, CE, ERIFLEX UD, RoHS, cUR, CSA
UD-400112AL	569252	185 mm ²	10 mm ²	1000, 1500	1000	RoHS, cUR, CSA, UR, CE, ERIFLEX UD
UDF-500A	569060	185 mm ²	35 mm ²	1000	600	UR, CE, ERIFLEX UD, RoHS, cUR
UD-400A	569050	185 mm ²	35 mm ²	1000	600	CE, ERIFLEX UD, UR, RoHS, cUR, CSA
UD-250A	569040	120 mm ²	35 mm ²	1000	600	cUR, CSA, RoHS, CE, ERIFLEX UD, UR
UDF12C800AL	569208	240 mm ²	25 mm ²	1000, 1500	1000	UL, cUL, QPQS7.E49727 6
UDF12C500AL	569206	100 mm ²	25 mm ²	1000, 1500	1000	cUL, QPQS7.E49727 6, UL

DETALHES ADICIONAIS DO PRODUTO

Increase the number of outputs with one input using a jumper on blocks with a Max Current Rating, IEC up to 160 A.

Blocks with 1,000 VAC/DC Max Working Voltage, UL are ideal for solar applications.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE