

nVent CADDY Telescoping Pipe Stand

The nVent CADDY Telescoping Pipe Stand is an adjustable and flexible solution for supporting horizontal pipe runs using a traditional V-Saddle or bolt flange attachment method. The design ensures a faster installation that quickly adapts to a variety of pipe sizes and heights from the floor. The unique V-bolt fastener—with built in nVent CADDY Rod Lock Technology and flange attachment tabs—can adapt to a large range of bolt patterns, sizes and pipe diameters, ultimately reducing inventory and the amount of components needed with over two-thirds savings. Offering a complete out-of-the-box assembly, the nVent CADDY Telescoping Pipe Stand is a contemporary solution for pipe runs.







FEATURES

- Supports and fastens low-to-the-ground horizontal pipe runs
- Telescoping post provides fast vertical height adjustment
- Designed to minimize fabrication and reduce installation time of a complete stand compared to traditional methods
- Integrated weep hole at bottom of stand provides drainage for condensation
- Includes four holes for anchoring base to floor
- Conforms with Federal Specification WW-H-171 (Type 36, 37, 38, 39), Manufacturers Standardization Society ANSI/MSS SP-58 (Type 36, 37, 38)

Material: Steel
 Finish: Electrogalvanized
 Certifications: OSHPD/HCAI
 Static Load Safety Factor: 3.5:1

Part Number	Pipe Size	A	B	C	D	Hole Size HS	Static Load F	Unit Weight
CTS04	1–5"	20.000"–40-1/2"	6.812"	6-1/2"	5"	5/8"	1370 lb	26 lb
CTS10	5–10"	23.000"–49-7/8"	14-3/8"	8-1/2"	6-1/2"	5/8"	1740 lb	35.5 lb
CTSS04	1–5"	13.437"–21.812"	6.812"	6-1/2"	5"	5/8"	1370 lb	18.51 lb
CTSS10	5–10"	16.000"–25-7/8"	14-3/8"	8-1/2"	6-1/2"	5/8"	1740 lb	31.52 lb
CTS10A24	12–24"	7.56 Min	27	1.33	–	–	–	7.49 lb



Part Number	Pipe Size	A	B	C	D	E	F	G	BS	HS
CTSS04	1"	13-7/16"-19-7/8"	6-13/16"	6-1/2"	5"	3-1/16"-6-1/16"	1370 lb	15-15/16"-23-7/16"	1/2"-5/8"	5/8"
	1-1/4"	13-5/8"-20-1/8"								
	1-1/2"	13-13/16"-20-1/4"								
	2"	14"-20-1/2"								
	3"	14-11/16"-21-3/16"								
4"	15-5/16"-21-13/16"									
CTS04	1"	21-3/16"-36-1/2"	6-13/16"	6-1/2"	5"	3-1/16"-6-1/16"	1370 lb	23-11/16"-38"	1/2"-5/8"	5/8"
	1-1/4"	21-3/8"-36-11/16"								
	1-1/2"	21-1/2"-36-13/16"								
	2"	21-3/4"-37-1/16"								
	3"	22-7/16"-37-3/4"								
4"	23-1/16"-38-5/16"									
CTSS10	5"	16"-22-7/8"	14-3/8"	8-1/2"	6-1/2"	3-1/16"-6-1/16"	1740 lb	15-15/16"-23-7/16"	3/4"-1-1/4"	5/8"
	6"	16-5/8"-23-1/2"								
	8"	17-3/4"-24-5/8"								
	10"	19"-25-7/8"								
CTS10	5"	23-13/16"-39-1/8"	14-3/8"	8-1/2"	6-1/2"	3-1/16"-6-1/16"	1740 lb	15-15/16"-23-7/16"	3/4"-1-1/4"	5/8"
	6"	24-7/16"-39-3/4"								
	8"	25-5/8"-40-15/16"								
	10"	26-13/16"-42-1/8"								
CTSS10 With CTS10A24	12"	20-3/16"-27"	27"	8-1/2"	6-1/2"	N/A	1740 lb	N/A	N/A	-
	14"	20-7/8"-27-3/4"								
	16"	22"-28-7/8"								
	18"	23-3/16"-30-1/16"								
	20"	24-3/8"-31-3/16"								
24"	26-11/16"-33-1/2"									
CTS10 With CTS10A24	12"	28"-43-5/16"	27"	8-1/2"	6-1/2"	N/A	1740 lb	N/A	N/A	-
	14"	28-11/16"-44"								
	16"	29-7/8"-45-3/16"								
	18"	31"-46-3/8"								
	20"	32-3/16"-47-1/2"								
24"	34-1/2"-49-13/16"									

When insulating pipe install V-bolt after insulation.

CTS04 can accommodate pipe sizes from 1" through 4" when v-bolt is used. CTS10 can accommodate pipe sizes from 5" through 8" when v-bolt is used. Installer must determine weight of the pipe and proper spacing when supporting larger sizes.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE