


Self-regulating heating cable

HEATING CABLE CONSTRUCTION



Electrical heat-tracing for process temperature maintenance applications up to 121°C which may be subject to steam cleaning.

The nVent RAYCHEM XTV family of self-regulating, parallel circuit heating cables is used for process temperature maintenance of pipes and vessels.

It can also be used for frost protection of large pipes and for applications requiring high temperature exposure capability.

APPLICATION

Area classification	Hazardous, Zone 1, Zone 2 (Gas), Zone 21, Zone 22 (Dust) Ordinary
Traced surface type	Carbon steel Stainless steel Painted or unpainted metal
Chemical resistance	Organics and corrosives For aggressive organics and corrosives consult your local nVent representative

SUPPLY VOLTAGE

230 Vac (Contact your local nVent representative for data on other voltages)

APPROVALS (*)

SGS20ATEX0049X

II 2 G Ex 60079-30-1 eb IIC T* Gb or Ex 60079-30-1 eb mb IIC T* Gb

II 2 D Ex 60079-30-1 tb IIIC T**°C Db or Ex 60079-30-1 mb tb IIIC T**°C Db

Tmin -60°C (* See schedule)

IECEX BAS 20.0012X

Ex 60079-30-1 eb IIC T* Gb or Ex 60079-30-1 tb IIIC T**°C Db

Ex 60079-30-1 eb mb IIC T* Gb or Ex 60079-30-1 mb tb IIIC T**°C Db

Tmin -60°C (*see schedule)

The XTV heating cables are approved by DNV for use on ships and mobile offshore units.

DNV Certificate No. DNV-GL TAE00000TV



TC RU C-BE.MЮ62.B.00054/18

1Ex e IIC T* Gb X 1Ex e mb IIC T* Gb X

Ex tb IIIC T* Db X Ex tb mb IIIC T* Db X

Ta -60°C...+56°C IP66

000 "ТехИмпорт"



Ex e IIC T2/T3 Gb

Ex tD A21 IP66 T300°C/T200°C

SPECIFICATIONS

Maximum maintain or continuous exposure temperature (power on) 121°C

Maximum intermittent exposure temperature (power on/off) 250°C (*)
Maximum cumulative exposure 1000 hours
(*) The 250°C rating applies to all products printed "MAX INTERMITTENT EXPOSURE 250C".

Temperature classification
T2: 20XTV2-CT-T2
T3: 4XTV2-CT-T3, 8XTV2-CT-T3, 12XTV2-CT-T3, 15XTV2-CT-T3

Based on systems approach* T3-T6
* nVent RAYCHEM XTV heat-tracing cables are approved for the listed temperature classifications by using the principles of stabilized design (as per system classification approach) or the use of a temperature limiting device.
Use TraceCalc design software or contact nVent.


Minimum installation temperature -60°C

Minimum bend radius
-60°C ≤ T < -20°C: 51 mm
-20°C ≤ T < -10°C: 35 mm
-10°C ≤ T < 0°C: 25 mm
0°C ≤ T < +10°C: 20 mm
T ≥ +10°C: 12 mm

THERMAL OUTPUT RATING

Nominal power output at 230 Vac on insulated steel pipes

A 20XTV2-CT-T2
B 15XTV2-CT-T3
C 12XTV2-CT-T3
D 8XTV2-CT-T3
E 4XTV2-CT-T3



	4XTV2-CT-T3	8XTV2-CT-T3	12XTV2-CT-T3	15XTV2-CT-T3	20XTV2-CT-T2
Nominal power output (W/m at 10°C)	12	25	38	47	63

PRODUCT DIMENSIONS (NOMINAL) AND WEIGHT

Thickness (mm)	7.2	7.2	7.2	7.2	7.2
Width (mm)	11.7	11.7	11.7	11.7	11.7
Weight (g/m)	170	170	170	170	170

MAXIMUM CIRCUIT LENGTH BASED ON TYPE 'C' CIRCUIT BREAKERS ACCORDING TO EN 60898

Electrical protection sizing	Start-up temperature	Maximum heating cable length per circuit (m)				
		16 A	-20°C	145	90	65
	+10°C	170	105	75	60	45
25 A	-20°C	225	145	105	85	65
	+10°C	245	165	120	95	70
32 A	-20°C	245	175	135	105	80
	+10°C	245	175	140	125	90
40 A	-20°C	245	175	140	135	110
	+10°C	245	175	140	135	110

The above numbers are for circuit length estimation only. For more detailed information please use the nVent TraceCalc software or Contact your local nVent representative. nVent requires the use of a 30 mA residual current device to provide maximum safety and protection from fire. Where design results in higher leakage current, the preferred trip level for adjustable devices is 30 mA above any inherent capacitive leakage characteristic of the heater as specified by the trace heater supplier or alternatively, the next common available trip level for non adjustable devices, with a maximum of 300 mA. All safety aspects need to be proven.

ORDERING DETAILS

Part description	4XTV2-CT-T3	8XTV2-CT-T3	12XTV2-CT-T3	15XTV2-CT-T3	20XTV2-CT-T2
Part No. (*)	P000001667	P000001670	P000001673	P000001675	P000001677

COMPONENTS

nVent offers a full range of components for power connections, splices and end seals. These components must be used to ensure proper functioning of the product and compliance with electrical requirements.

(*) Localized versions may exist with limited approvals and different part numbers. Contact your local sales representative.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nVent.com

Europe, Middle East, Africa

Tel +32.16.213.502
 Fax +32.16.213.604
 thermal.info@nVent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nVent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nVent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER